

Order No.: 5LZ902050TW | **GTIN (EAN):** 4058352145807

Product description: SCon41Rotrot.dimm,rot/push-bttn,rec




SITECO Connect 41 Rotaryrotary dimmer, master, local control - self-sufficient standalone sensors, dimmable, installation type: recessed, installation location: in the switch box, of plastic, protection rating (complete): IP20, insulation class (complete): insulation class II (safety insulation), certification: CE, voltage: 230V, voltage type: AC, 1 x rotary button/push button, 1 x DALI, packaging unit: 1 piece

IP 20 □ (∈

Wt. (kg): 0.1

GTIN (EAN): 4058352145807





Order No.: 5LZ902050TW | GTIN (EAN): 4058352145807

Detailed technical description: SCon41Rotrot.dimm,rot/push-bttn,rec



Key data

- System family: SITECO Connect 41
- Product type: rotary dimmer
- Product name: SITECO Connect 41 Rotary
- Order No.: 5LZ902050TW

Lighting technology | Lamps | Control gear

Component 1

Operating device:

- Control: DALI, dimmable

Certificates, Standards

- Protection rating: IP20
- Insulation class: insulation class II (safety insulation)
- Temperature range (operation): -5..+45°C
- Certification, designation: CE

Material, Colour

- installation housing: plastic, grey
- Colour specification: grey

Mounting

- Mounting method, mounting location: recessed, in the switch box
- Supplement: only suitable for use in indoor areas

Electrical connection

- Nominal voltage: 230V, 50/60Hz, AC

Dimensions, Weight

Length: 80mmWidth: 80mmHeight: 32mmWeight: 0.1kg

Inputs

1x rotary button/push button

 Connection: screw terminal, 2-pole, max. 4.0mm²

Outputs

1x DALI

- Connection: screw terminal, 2-pole, max. 4mm²
- Limiting: max. 25x ECG DALI
- Feature: ON/OFF, bright/dark, storing of brightness power on illumination levels, expansion of control units or number of ECG DALI via parallel switching of several rotary potentiometers; incl. rotary button and frame of white plastic
- Cable length: max. 300m



Order No.: 5LZ902050TW | **GTIN (EAN):** 4058352145807

Dimensions: SCon41Rotrot.dimm,rot/push-bttn,rec

